

# YCR32RG7

By Burndy  
Catalog # YCR32RG7

Aluminum Reducer, Designed for joining (i) Cu to Alum. or ACSR (ii) Alum or ACSR to Alum. or ACSR, Barrels Partially filled with PENETROX™ and Sealed.



## General

Connector Type	Reducer
Die Index	317;705
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYREDUCER™
UPC	781810014929
UPC 12 Digit	7818100149299

## Dimensions

Dimension - B Length inch	3 in
Dimension - L Length Overall mm	170 mm
Dimension - Length Overall inch	6.69 in
Dimension - Outside Diameter inch	1.25 in

## Conductor Related

Conductor - ACSR Str Size A	336.4 (18/1) Merlin;336.4 (26/7) Linnet
Conductor - ACSR Str Size A Range	336.4 (18/1) Merlin-336.4 (26/7) Linnet
Conductor - ACSR Str Size B	336.4 (18/1) Merlin;336.4 (26/7) Linnet
Conductor - ACSR Str Size B Range	336.4 (18/1) Merlin-336.4 (26/7) Linnet
Conductor - AL Str Size A	350 kcmil;397.5 kcmil
Conductor - AL Str Size A Range	350 kcmil-397.5 kcmil
Conductor - AL Str Size B	350 kcmil;397.5 kcmil
Conductor - AL Str Size B Range	350 kcmil-397.5 kcmil
Conductor - Copper Str Size A	350 kcmil
Conductor - Copper Str Size A Range	350 kcmil
Conductor - Copper Str Size B	350 kcmil
Conductor - Copper Str Size B Range	350 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size A</li> <li>• AL C Str-Size A</li> <li>• CU C Str-Size A</li> <li>• ACSR C Str-Size B</li> <li>• AL C Str-Size B</li> <li>• CU C Str-Size B</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	3920

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - SD057607-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YCR32RG7-SPEC-EN | REV 8/2023