

YCS25, Copper Loop Splice

By Burndy
Catalog # YCS25

CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, -3/8 IN L.



Application

For Copper Conductors

General

Connector Type	Splice
Construction Material - Main	Copper
Die Index	165
EU RoHS Indicator	Yes
Material	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS
UPC	781810014172
UPC 12 Digit	7818100141722

Dimensions

Dimension - B Length fraction	1-8/17 in
Dimension - B Length inch	1.47 in
Dimension - Inside Diameter inch	0.41 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.09 in
Dimension - Outside Diameter inch	0.63 in

Conductor Related

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	9800

Product Assets

[Sales Drawings - 15042](#)