

# YCS25R, Aluminum Sleeve, Staked Cable Stop

By Burndy  
Catalog # YCS25R



HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), 7-1/8 IN L.

## Application

For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

## General

Catalog Number	YCS25R
Connector Type	Splice
Die Index	243
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810820513
UPC 12 Digit	7818108205133

## Dimensions

Dimension - B Length inch	3.48 in
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in
Dimension - Outside Diameter inch	0.62 in

## Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 (7, 19) AWG
Conductor - AL Str Size Range	1/0 (7, 19) AWG

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	9800

## Product Assets

- [3D Models - YCS25R\\_MODEL-IGES](#)
- [3D Models - YCS25R\\_MODEL-STEP](#)
- [3D Models - YCS25R\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YCS-R\\_LineArt](#)
- [Sales Drawings - 50115707](#)
- [Specifications - YCS25R](#)