

YCS26, Copper Loop Splice

By Burndy
Catalog # [YCS26](#)



CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, Die index:166.

Features

- Copper Loop Splice
- Designed to withstand jumper loop tensile and vibration stress up to 60 percent of Rated Breaking Strength

Application

For Copper Conductors

General

Catalog Number	YCS26
Connector Type	Splice
Die Index	166
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of	3
Crimps Required	
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS
UPC	781810014189
UPC 14 Digit GTIN	00781810014189

Dimensions

Dimension - A Outside	0.71 in
Diameter inch	
Dimension - B Length fraction	1-36/61 in
Dimension - B Length inch	1.59 in
Dimension - B Outside	0.71 in
Diameter inch	

Dimension - L Length Overall	85 mm
mm	
Dimension - Length Overall	3.34 in
inch	

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Range	

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YCS-A_LineArt](#)
[Sales Drawings - 15042](#)
[Specifications - YCS26](#)

