

YCS27, Aluminum Loop Splice

By Burndy
Catalog # YCS27

CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, 3-1/4 IN L.



General

Connector Type	Splice
Die Index	167
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810014202
UPC 12 Digit	7818100142022

Dimensions

Dimension - A Outside Diameter inch	0.79 in
Dimension - B Length fraction	1-14/25 in
Dimension - B Length inch	1.56 in
Dimension - B Outside Diameter inch	0.79 in
Dimension - L Length Overall mm	83 mm
Dimension - Length Overall inch	3.27 in

Conductor Related

Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	7400

Product Assets

[Sales Drawings - 15042](#)