

YCS28, Copper Loop Splice

By Burndy
Catalog # YCS28

CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, 3-1/8 IN L.



Application

For Copper Conductors

General

Connector Type	Splice
Die Index	168
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	3
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS
UPC	781810014219
UPC 12 Digit	7818100142199

Dimensions

Dimension - A Outside Diameter inch	0.89 in
Dimension - B Length fraction	1-8/17 in
Dimension - B Length inch	1.47 in
Dimension - B Outside Diameter inch	0.89 in
Dimension - L Length Overall mm	78 mm
Dimension - Length Overall inch	3.09 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	5800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YCS-A_LineArt](#)
[Sales Drawings - 15042](#)