



YCS361R, Aluminum Sleeve, Staked Cable Stop

By Burndy
Catalog # [YCS361R](#)

HYSPLICE AL sleeve with staked cable stop, designed to withstand jumper loop tensile and vibration stresses. ANSI C119.4 CLASS 2 (PARTIAL TENSION), Index: 327.

Features

- HYSPLICE Sleeve designed to withstand jumper loop tensile and vibration stresses
- Made of aluminum with staked-in cable stop
- Pre-Filled with PENETROX Joint Compound and Capped

Application


For ACSR, All Aluminum, 6201, 5005 And Compressed Conductors

General

Catalog Number	YCS361R
Connector Type	Splice
Die Index	327
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YCS-R
UPC	781810820575
UPC 14 Digit GTIN	00781810820575

Dimensions

Dimension - B Length fraction	4-3/50 in
Dimension - B Length inch	4.06 in
Dimension - L Length Overall mm	210 mm
Dimension - Length Overall inch	8.25 in



Dimension - Outside Diameter 1.3 in
inch

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) kcmil
Conductor - AL Str Size	477 kcmil (18/1)
Conductor - AL Str Size Range	477 kcmil

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	3600

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCS-R_LineArt](#)
- [Sales Drawings - 50115707](#)
- [Specifications - YCS361R](#)



A Hubbell brand