

YCS39, Copper Loop Splice

By Burndy
Catalog # YCS39

CU loop splice connector designed to withstand jumper loop tensile and vibration stresses up to 60 percentage RBS, Index: 627.



General

Connector Type	Splice
Die Index	627
Material	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810014271
UPC 12 Digit	7818100142711

Dimensions

Dimension - A Outside Diameter inch	1.7 in
Dimension - B Length fraction	3 in
Dimension - B Length inch	3.01 in
Dimension - B Outside Diameter inch	1.7 in
Dimension - Inside Diameter inch	1.06 in
Dimension - L Length Overall mm	175 mm
Dimension - Length BB inch	3.01 in
Dimension - Length Overall inch	6.88 in

Conductor Related

Conductor - Copper Str Size	750 kcmil
Conductor - Copper Str Size Range	750 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	480

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YCS-A_LineArt](#)
[Sales Drawings - 15042](#)