



YCU26, Copper Repair Sleeve

By Burndy
Catalog # [YCU26](#)

Sheet Cu Repair Sleeve For Compression Splices(Single Sleeve
Jumper Normal Tension), 2/0 AWG Cu, 166 Index.

General

Catalog Number	YCU26
Connector Type	Splice
Die Index	166
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810014387
UPC 14 Digit GTIN	00781810014387

Dimensions

Dimension - Height fraction	39/47 in
Dimension - Height inch	0.83 in
Dimension - Height mm	21 mm
Dimension - L Length Overall mm	150 mm
Dimension - Length Overall inch	5.91 in
Dimension - Width fraction	37/50 in
Dimension - Width inch	0.74 in

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Copper Str Size Range	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	4350

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YCS-A_LineArt](#)
- [Sales Drawings - SC24522-01_A](#)
- [Specifications - YCU26](#)

