



# YDS021R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy  
Catalog # [YDS021R](#)



2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension), Conductor:2(7/1) Sparate.

## General

Connector Type	Splice
Die Index	242;241
Die Index - Element A	242
Die Index - Element B	241
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015292
UPC 12 Digit	7818100152922

## Dimensions

Dimension - Aluminum Sleeve Length inch	17 in
Dimension - Steel Sleeve Length inch	4.75 in

## Conductor Related

Conductor - ACSR Cmpt Size	2 AWG
Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - ACSR Str Size	2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (7/1) Sparate AWG
Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SA..039024-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YDS021R-SPEC-EN | REV 8/2023