



# YDS1RL, Aluminum Full Tension Splice, #1 AWG ACSR

By Burndy  
Catalog # [YDS1RL](#)



Al Compression Full Tension Splice, #1 AWG ACSR.

## General

Connector Type	Splice
Die Index	245
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	621945255876
UPC 12 Digit	6219452558766

## Dimensions

Dimension - L Length Overall mm	356 mm
Dimension - Length Overall inch	14 in
Dimension - Outside Diameter inch	0.71 in

## Conductor Related

Conductor - ACSR Str Size	1 (6/1) Robin AWG
Conductor - ACSR Str Size Range	1 (6/1) Robin AWG
Conductor - AL Str Size	1 AWG
Conductor - AL Str Size Range	1 AWG
Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

## Product Assets

[3D Models - YDS1RL\\_MODEL-IGES](#)  
[3D Models - YDS1RL\\_MODEL-PDF](#)  
[3D Models - YDS1RL\\_MODEL-STEP](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sd034930-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YDS1RL-SPEC-EN | REV 8/2023