



# YDS25AT, Aluminum Full Tension Sleeve Splice

By Burndy  
Catalog # [YDS25AT](#)



Aluminium Hysplice, 7-1/4 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors, Die index: 243.

## Application

For All Aluminum Compressed And Compact Conductors

## General

Color Code	Yellow
Connector Type	Splice
Die Index	BG or 243
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810820971
UPC 12 Digit	7818108209711

## Dimensions

Dimension - B Length fraction	3-53/93 in
Dimension - B Length inch	3.57 in
Dimension - L Length Overall mm	185 mm
Dimension - Length Overall inch	7.27 in
Dimension - Outside Diameter inch	0.62 in

## Conductor Related

Conductor - ACSR Cmpt Size	1/0 AWG
Conductor - ACSR Cmpt Size Range	1/0 AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	9800

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Product Cross Section Image\(s\) - BUR\\_YDS-AT\\_LineArt](#)  
[Sales Drawings - SD..021880-01](#)



A proud member of the Hubbell Family.