



## YDS261R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy  
Catalog # [YDS261R](#)



Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension).

### General

Connector Type	Splice
Die Index	305;316
Die Index - Element A	305
Die Index - Element B	316
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810099698
UPC 12 Digit	7818100996988

### Dimensions

Dimension - Aluminum Sleeve Length inch	22.25 in
Dimension - L Length Overall mm	219 mm
Dimension - Length Overall inch	8.63 in
Dimension - Steel Sleeve Length inch	8.625 in

### Conductor Related

Conductor - ACSR Str Size	134.6 (12/7) Leghorn kcmil
Conductor - ACSR Str Size Range	134.6 (12/7) Leghorn kcmil
Conductor - AL Str Size	134.6 (12-7)
Conductor Type	<ul style="list-style-type: none"><li>ACSR C Str-Size</li><li>AL C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	15
Minimum Pack Quantity	1
Pallet Quantity	900

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SA..039024-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YDS261R-SPEC-EN | REV 5/2024