



## YDS26R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy  
Catalog # [YDS26R](#)



2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension), Conductor: 2/0 (6/1) Quail.

### General

Connector Type	Splice
Die Index	242;245
Die Index - Element A	242
Die Index - Element B	245
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015513
UPC 12 Digit	7818100155133

### Dimensions

Dimension - Aluminum Sleeve Length inch	19.75 in
Dimension - B Length inch	19.75 inch
Dimension - L Length Overall mm	502 mm
Dimension - Length Overall inch	19.73 in
Dimension - Outside Diameter inch	0.7 in
Dimension - Steel Sleeve Length inch	5.25 in

### Conductor Related

Conductor - ACSR Cmpt Size	2/0 AWG
Conductor - ACSR Cmpt Size Range	2/0 AWG
Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/0 (6/1) Quail AWG
Conductor Type	<ul style="list-style-type: none"><li>ACSR C Str-Size</li><li>AL C Str-Size</li></ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	1920

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SA..039024-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YDS26R-SPEC-EN | REV 8/2023