



YDS271R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS271R](#)



Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension).

General

Connector Type	Splice
Die Index	255;317
Die Index - Element A	255
Die Index - Element B	317
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810090923
UPC 12 Digit	7818100909233

Dimensions

Dimension - Aluminum Sleeve Length inch	25.625 in
Dimension - L Length Overall mm	203 mm
Dimension - Length Overall inch	8 in
Dimension - Steel Sleeve Length inch	8 in

Conductor Related

Conductor - ACSR Str Size	159 (12/7) Guinea kcmil
Conductor - ACSR Str Size Range	159 (12/7) Guinea kcmil
Conductor Type	<ul style="list-style-type: none">ACSR C Str-SizeAL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SA..039024-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YDS271R-SPEC-EN | REV 8/2023