

YDS27AT, Aluminum Full Tension Sleeve

By Burndy
Catalog # [YDS27AT](#)



Aluminium Hysplice, 7-1/4 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors, Die index: 247.

Application

For All Aluminum Compressed And Compact Conductors

General

Catalog Number	YDS27AT
Connector Type	Splice
Die Index	247
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810015544
UPC 12 Digit	7818100155444

Dimensions

Dimension - B Length fraction	3-14/25 in
Dimension - B Length inch	3.56 in
Dimension - L Length Overall mm	184 mm
Dimension - Length Overall inch	7.25 in
Dimension - Outside Diameter inch	0.77 in

Conductor Related

Conductor - ACAR Str Size	3/0 (7) AWG
Conductor - ACAR Str Size Range	3/0 (7) AWG
Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	9800

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YDS-AT_LineArt](#)
- [Sales Drawings - SD..021880-01](#)
- [Specifications - YDS27AT](#)