



YDS2C3, Copper Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS2C3](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: #2 (3) Cu STR (Hard, Medium, or Soft Drawn), Die Index: 163, Made of copper tubing, Installed with standard tools and dies.

Application

For Stranded Copper Conductors

General

| | |
|--|--------------|
| Connector Type | Splice |
| Die Index | 163 |
| EU RoHS Indicator | Yes |
| Material | Copper |
| Oxide Inhibitor Type | Penetrox E |
| Physical Attribute - Number of Crimps Required | 2 |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | HYSPLICE |
| Trade Name | HYSPLICE™ |
| Type | YDS - C |
| UPC | 781810820919 |

Dimensions

| | |
|-----------------------------------|------------|
| Dimension - B Length fraction | 1-18/25 in |
| Dimension - B Length inch | 1.72 in |
| Dimension - L Length Overall mm | 94 mm |
| Dimension - Length Overall inch | 3.69 in |
| Dimension - Outside Diameter inch | 0.53 in |

Conductor Related

Conductor - Copper Str Size 2 AWG

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | RUS |
| Standards - Industry Standards Met | RUS |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 100 |
| Minimum Pack Quantity | 100 |
| Pallet Quantity | 11100 |

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50115709](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YDS2C3-SPEC-EN | REV 8/2023