



YDS2CA, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy
Catalog # [YDS2CA](#)



Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension), Conductor:2(7).

Application

For All Aluminum Compressed And Compact Conductors

General

Catalog Number	YDS2CA
Connector Type	Splice
Die Index	163
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-A
UPC	781810015339
UPC 12 Digit	7818100153399

Dimensions

Dimension - B Length fraction	1-22/25 in
Dimension - B Length inch	1.88 in
Dimension - Inside Diameter inch	1 in
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.88 in
Dimension - Outside Diameter inch	0.5 in

Conductor Related

Conductor - ACAR Str Size	2 (7) AWG
Conductor - ACAR Str Size Range	2 (7) AWG
Conductor - ACSR Cmpt Size	2 AWG
Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	9000

Product Assets

- [3D Models - YDS2CA_MODEL-PDF](#)
- [3D Models - YDS2CA_MODEL-IGES](#)
- [3D Models - YDS2CA_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YDS-A_LineArt](#)
- [Sales Drawings - SC019521-01](#)
- [Specifications - YDS2CA](#)



A Hubbell brand