



YDS2R, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS2R](#)



2-piece, full tension ACSR splice consists of steel inner sleeve and AL outer sleeve, ANSI C119.4 Class 1 (Full Tension).

General

Connector Type	Splice
Die Index	239
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015346
UPC 12 Digit	7818100153466

Dimensions

Dimension - L Length Overall mm	349 mm
Dimension - Length Overall inch	13.75 in

Conductor Related

Conductor - ACSR Cmpt Size	2 AWG
Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SA..039024-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YDS2R-SPEC-EN | REV 8/2023