



YDS30, Copper Single Sleeve Full Tension Splice



By Burndy
Catalog # [YDS30](#)

CU Full Tension Splice, Accommodates Wire: 300 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 170

Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Stranded Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Yes
Certification - cULus	No
Buy America(n) Qualified	• Buy America Compliant (All status valid till December 2026) • Buy American Act Compliant (All status valid till December 2026) • BABA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	300 kcmil
-----------------------------	-----------

Configuration

Physical Attribute - Number of	3
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	205 mm
Dimension - Outside Diameter inch	1.05 in
Dimension - B Length fraction	3-43/50 in
Dimension - B Length inch	3.86 in
Dimension - Length Overall inch	8.09 in

General

Product Family	Utility Overhead & Underground Distribution>Splices>YCS/YDS (Full Tension)
Trade Name	HYSPLICE™
Die Index	170
Oxide Inhibitor Type	Penetrox E
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYSPLICE
Product Type	Compression
UPC	781810014653
Type	YDS
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014653

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)