



YDS301AT, Aluminum Full Tension Sleeve

By Burndy
Catalog # [YDS301AT](#)

Hysplice, 336.4 (19, 37), 9-7/8 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors.



Application

For All Aluminum Compressed And Compact Conductors

General

Catalog Number	YDS301AT
Connector Type	Splice
Die Index	321
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810015902
UPC 12 Digit	7818100159022

Dimensions

Dimension - B Length fraction	4-22/25 in
Dimension - B Length inch	4.88 in
Dimension - L Length Overall mm	251 mm
Dimension - Length Overall inch	9.88 in
Dimension - Outside Diameter inch	1.06 in

Conductor Related

Conductor - ACSR Cmpt Size	336.4
Conductor - ACSR Cmpt Size Range	336.4
Conductor - ACSR Str Size	336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	336.4 (18/1) Merlin-336.4 (30/7) Oriole
Conductor - AL Str Size	336.4
Conductor - AL Str Size Range	336.4
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	30
Minimum Pack Quantity	1
Pallet Quantity	2700

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YDS-AT_LineArt](#)
- [Sales Drawings - SD..021880-01](#)
- [Specifications - YDS301AT](#)



A Hubbell brand