

YDS311AT, Aluminum Full Tension Sleeve

By Burndy
Catalog # [YDS311AT](#)



Al Full Tension Sleeve Splice, 397.5 kcmil(Al), 12.22" L, 468 Index.

Features

- Full-Tension sleeve made of aluminum tubing with staked-in cable stop
- Sizes 1/0 and larger feature a taper for gradual transition of stress
- Pre-Filled with PENETROX Joint Compound and Capped

Application

For All Aluminum Compressed And Compact Conductors

General

Catalog Number	YDS311AT
Connector Type	Splice
Die Index	468
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810015933
UPC 12 Digit	7818100159333

Dimensions

Dimension - B Length fraction	6-1/20 in
Dimension - B Length inch	6.05 in
Dimension - L Length Overall mm	310 mm
Dimension - Length Overall inch	12.22 in
Dimension - Outside Diameter inch	1.19 in

Conductor Related

Conductor - ACSR Str Size	397.5 (18/1) Chickadee
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee
Conductor - AL Str Size	397.5(19)kcmil
Conductor - AL Str Size Range	397.5
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	1680

Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YDS-AT_LineArt](#)
- [Sales Drawings - SD..021880-01](#)
- [Specifications - YDS311AT](#)