



YDS32, Copper Full Tension Splice

By Burndy
Catalog # [YDS32](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 400 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 209, Made of copper tubing, Installed with standard tools and dies.

General

Connector Type	Splice
Die Index	209
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	5
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810014660

Dimensions

Dimension - B Length fraction	6-1/4 in
Dimension - B Length inch	6.25 in
Dimension - L Length Overall mm	326 mm
Dimension - Length Overall inch	12.83 in
Dimension - Outside Diameter inch	1.24 in

Conductor Related

Conductor - Copper Str Size 400 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	702

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50115709](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YDS32-SPEC-EN | REV 8/2023