

YDS321RLY, 1-piece ACSR Splice

By Burndy

Catalog # [YDS321RLY](#)



One piece full tension aluminum splice designed to eliminate possible basketing of conductor. Installed by crimping from end of connector towards the center, Accommodates ACSR with aluminized steel core: 336.4 ACSR (18-1), 336.4 AAC (19).

Application

For ACSR, Aluminum, 6201 And 5005 Conductors

General

Catalog Number	YDS321RLY
Connector Type	Splice
Die Index	655
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	UNISPLICE
Trade Name	UNISPLICE™
Type	YDS-RLY
UPC	781810015940
UPC 12 Digit	7818100159400

Dimensions

Dimension - L Length Overall mm	521 mm
Dimension - Length Overall inch	20.5 in

Conductor Related

Conductor - ACSR Str Size	336.4 (18/1) Merlin
Conductor - ACSR Str Size Range	336.4 (18/1) Merlin
Conductor - AL Str Size	336.4
Conductor - AL Str Size Range	336.4
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	20
Minimum Pack Quantity	20
Pallet Quantity	1440

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YDS-RLY_LineArt](#)
- [Sales Drawings - SD..053576-01](#)
- [Specifications - YDS321RLY](#)