



## YDS34, Copper Single Sleeve Full Tension Splice

By Burndy  
Catalog # YDS34



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 500 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 210, Made of copper tubing, Installed with standard tools and dies.

### Application

For Stranded Copper Conductors

### General

Catalog Number	YDS34
Connector Type	Splice
Die Index	210
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of	5
Crimps Required	
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810014677

### Dimensions

Dimension - B Length fraction	5-3/4 in
Dimension - B Length inch	5.75 in
Dimension - L Length Overall mm	295 mm
Dimension - Length Overall inch	11.62 in
Dimension - Outside Diameter inch	1.38 in

### Conductor Related

Conductor - Copper Str Size 500 kcmil

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	585

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YDS\\_LineArt](#)  
[Sales Drawings - 50115709](#)  
[Specifications - YDS34](#)



A Hubbell brand