

## YDS341RL, Full Tension Splice

By Burndy  
Catalog # [YDS341RL](#)

Full Tension Splice, 397.5 kcmil ACSR (18-1) 419.6 kcmil 5005, 327 Index.



### General

Catalog Number	YDS341RL
Connector Type	Splice
Die Index	327
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	781810821268
UPC 12 Digit	7818108212688

### Dimensions

Dimension - B Length fraction	10-9/10 in
Dimension - B Length inch	10.9 in
Dimension - L Length Overall mm	557 mm
Dimension - Length Overall inch	21.92 in
Dimension - Outside Diameter inch	1.31 in

### Conductor Related

Conductor - AAAC 5005 Size	465.4 (19) kcmil
Conductor - AAAC 5005 Size Range	465.4 (19) kcmil
Conductor - AAAC 6201 Size	465.4 (19) kcmil
Conductor - AAAC 6201 Size Range	465.4 (19) kcmil
Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil
Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	720

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YDS-RL\\_LineArt](#)  
[Sales Drawings - sd034930-01](#)  
[Specifications - YDS341RL](#)