

YDS361RLY, 1-piece Aluminum Full Tension Splice

By Burndy

Catalog # [YDS361RLY](#)

One piece full tension aluminum splice designed to eliminate possible basketing of conductor. Installed by crimping from end of connector towards the center.



General

Catalog Number	YDS361RLY
Connector Type	Splice
Die Index	788;720
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810042267
UPC 14 Digit GTIN	00781810042267

Dimensions

Dimension - B Length fraction	12-11/25 in
Dimension - B Length inch	12.44 in
Dimension - L Length Overall mm	635 mm
Dimension - Length Overall inch	25 in
Dimension - Outside Diameter inch	1.41 in

Conductor Related

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil

Conductor - AL Str Size	477(18-1)kcmil
Conductor - AL Str Size Range	477 kcmil
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	12
Minimum Pack Quantity	1
Pallet Quantity	720

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SD..053576-01](#)
[Specifications - YDS361RLY](#)