


YDS375H, Full Tension Steel Splice

By Burndy
Catalog # [YDS375H](#)



Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension), Die index: 304.

Application

For HS, EHS, Utilities (UT) Or Siemens-Martin (SM) Galvanized Steel Guy, Messenger, And Static Conductors

General

Connector Type	Splice
Die Index	304
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-H
UPC	781810016015
UPC 12 Digit	7818100160155

Dimensions

Dimension - B Length fraction	4-17/81 in
Dimension - B Length inch	4.21 in
Dimension - L Length Overall mm	230 mm
Dimension - Length Overall inch	9.07 in
Dimension - Outside Diameter inch	0.75 in

Conductor Related

Conductor - AL Coated Steel Size	3/8 (7) in
Conductor - AL Coated Steel Size Range	3/8 (7) in
Conductor - Galvanized Steel Str Size	3/8 (7) in
Conductor - Galvanized Steel Str Size Range	3/8 (7) in
Conductor - Grade	HS, UT
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	13
Minimum Pack Quantity	25
Pallet Quantity	1872

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SC18038-01](#)