



YDS39, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS39](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 750 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 627, Made of copper tubing, Installed with standard tools and dies.

General

Catalog Number	YDS39
Connector Type	Splice
Die Index	627
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	7
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810821121

Dimensions

Dimension - B Length fraction	6-1/100in
Dimension - B Length inch	6.01 in
Dimension - L Length Overall mm	325 mm
Dimension - Length Overall inch	12.78 in
Dimension - Outside Diameter inch	1.70 in

Conductor Related

Conductor - Copper Str Size	750 kcmil
-----------------------------	-----------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	3
Minimum Pack Quantity	1
Pallet Quantity	234

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YDS_LineArt](#)
[Sales Drawings - 50115709](#)
[Specifications - YDS39](#)