

YDS391AT, Aluminum, Full Tension Sleeve

By Burndy
Catalog # YDS391AT



Hysplice, 13-5/8 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors.

Application

For All Aluminum Compressed And Compact Conductors

General

Catalog Number	YDS391AT
Connector Type	Splice
Die Index	342
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-AT
UPC	781810821169
UPC 12 Digit	7818108211699

Dimensions

Dimension - B Length fraction	6-18/25 in
Dimension - B Length inch	6.72 in
Dimension - L Length Overall mm	344 mm
Dimension - Length Overall inch	13.56 in
Dimension - Outside Diameter inch	1.67 in

Conductor Related

Conductor - ACSR Str Size	795 (30/19) Mallard kcmil
Conductor - ACSR Str Size Range	795 (30/19) Mallard kcmil
Conductor - AL Str Size	800 kcmil
Conductor - AL Str Size Range	800 kcmil
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YDS-AT_LineArt](#)
- [Sales Drawings - SD..021880-01](#)
- [Specifications - YDS391AT](#)