



YDS39R44RS, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS39R44RS](#)



Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension).

General

Catalog Number	YDS39R44RS
Connector Type	Splice
Die Index	608;225
Die Index - Element A	225
Die Index - Element B	608
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810095492
UPC 12 Digit	7818100954922

Dimensions

Dimension - Aluminum Sleeve Length inch	32.50 in
Dimension - L Length Overall mm	663.7 mm
Dimension - Length Overall inch	26.13 in
Dimension - Outside Diameter inch	1.5 in
Dimension - Steel Sleeve Length inch	8 in

Conductor Related

Conductor - ACSR Str Size	556.5 (24/7) Parakeet;556.5 (26/7) Dove
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet-556.5 (26/7) Dove
Conductor - AL Str Size	556.5
Conductor - AL Str Size Range	556.5
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	350

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SA..039024-01](#)
- [Specifications - YDS39R44RS](#)