



YDS3C3, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS3C3](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: #3 (3) Cu STR (Hard, Medium, or Soft Drawn), Die Index: 163, Made of copper tubing, Installed with standard tools and dies.

General

| | |
|--|--------------|
| Connector Type | Splice |
| Die Index | 163 |
| Material | Copper |
| Oxide Inhibitor Type | Penetrox E |
| Physical Attribute - Number of Crimps Required | 3 |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | HYSPLICE™ |
| UPC | 781810014493 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 2-1/2 in |
| Dimension - B Length inch | 2.50 in |
| Dimension - L Length Overall mm | 133 mm |
| Dimension - Length Overall inch | 5.25 in |
| Dimension - Outside Diameter inch | 0.50 in |

Conductor Related

Conductor - Copper Str Size 3 AWG

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 9800 |

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_YDS_LineArt](#)
[Sales Drawings - 50115709](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YDS3C3-SPEC-EN | REV 5/2024