



YDS3K8, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # YDS3K8



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 3#8 COPPERWELD, Die Index: 205, Made of copper tubing, Installed with standard tools and dies.

General

Catalog Number	YDS3K8
Connector Type	Splice
Die Index	339
Material	Copper
Physical Attribute - Number of Crimps Required	5
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810014547

Dimensions

Dimension - B Length fraction	1-23/50 in
Dimension - B Length inch	2.46 in
Dimension - L Length Overall mm	133 mm
Dimension - Length Overall inch	5.22 in
Dimension - Outside Diameter inch	0.67 in

Conductor Related

Conductor - CopperWeld Str Size	3#8
---------------------------------	-----

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	3675

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_YDS_LineArt](#)
- [Sales Drawings - SC021055-01](#)
- [Specifications - YDS3K8](#)



A Hubbell brand