



## YDS44, Copper, Single Sleeve Full Tension Splice

By Burndy  
Catalog # YDS44



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 1000 kcmil Cu (Hard, Medium, or Soft Drawn), Die Index: 345, Made of copper tubing, Installed with standard tools and dies.

### General

Catalog Number	YDS44
Connector Type	Splice
Die Index	345
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	10
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810014684

### Dimensions

Dimension - B Length fraction	1-14/25 in
Dimension - B Length inch	7.56 in
Dimension - L Length Overall mm	387 mm
Dimension - Length Overall inch	15.25 in
Dimension - Outside Diameter inch	2.00 in

### Conductor Related

Conductor - Copper Str Size	1000 kcmil
-----------------------------	------------

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	3
Minimum Pack Quantity	1
Pallet Quantity	192

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_YDS\\_LineArt](#)
- [Sales Drawings - 50115709](#)
- [Specifications - YDS44](#)