



YDS451R49RS, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS451R49RS](#)



Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension).

General

Catalog Number	YDS451R49RS
Connector Type	Splice
Die Index	419;579
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810172032

Dimensions

Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	10 in

Conductor Related

Conductor - ACSR Str Size	795 (26/7) Drake
Conductor - ACSR Str Size Range	795 (26/7) Drake
Conductor - AL Str Size	795.5
Conductor - AL Str Size Range	795.5
Conductor Type	<ul style="list-style-type: none">ACSR C Str-SizeAL C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - SA..039024-01](#)
- [Specifications - YDS451R49RS](#)



A Hubbell brand