

YDS45LT, ACSR Full Tension Splice

By Burndy
Catalog # [YDS45LT](#)



Full Tension Splice, 927 kcmil ACSR, 648 Index.

General

Connector Type	Splice
Die Index	648
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	781810014196

Dimensions

Dimension - B Length fraction	10-31/50 in
Dimension - B Length inch	10.62 in
Dimension - L Length Overall mm	543 mm
Dimension - Length Overall inch	21.36 in
Dimension - Outside Diameter inch	2.25 in

Conductor Related

Conductor - AAAC 5005 Size	927.2 (37) kcmil
Conductor - AAAC 5005 Size Range	927.2 (37) kcmil
Conductor - AAAC 6201 Size	927.2 (37) kcmil
Conductor - AAAC 6201 Size Range	927.2 (37) kcmil
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	288

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - sd034930-01](#)