



YDS45R45RS, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy
Catalog # [YDS45R45RS](#)



Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension).

General

| | |
|---------------------------|--------------|
| Connector Type | Splice |
| Die Index | 320;352 |
| Die Index - Element A | 320 |
| Die Index - Element B | 352 |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | HYSPLICE™ |
| UPC | 781810290019 |

Dimensions

| | |
|---|----------|
| Dimension - Aluminum Sleeve Length inch | 32.50 in |
| Dimension - L Length Overall mm | 229 mm |
| Dimension - Length Overall inch | 9 in |
| Dimension - Steel Sleeve Length inch | 9 in |

Conductor Related

| | |
|---------------------------------|---|
| Conductor - ACSR Str Size | 795 (54/7) Condor |
| Conductor - ACSR Str Size Range | 795 (54/7) Condor |
| Conductor - AL Str Size | 795.5 |
| Conductor - AL Str Size Range | 795.5 |
| Conductor Type | <ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SA..039024-01](#)



A proud member of the Hubbell Family.