



# YDS45R45RS, 2-piece, ACSR Splice, includes inner and outer sleeves

By Burndy  
Catalog # [YDS45R45RS](#)



Two-piece, full tension ACSR splice consists of steel inner sleeve and aluminum outer sleeve. ANSI C119.4 Class 1 (Full Tension).

## General

Connector Type	Splice
Die Index	320;352
Die Index - Element A	320
Die Index - Element B	352
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810290019

## Dimensions

Dimension - Aluminum Sleeve Length inch	32.50 in
Dimension - L Length Overall mm	229 mm
Dimension - Length Overall inch	9 in
Dimension - Steel Sleeve Length inch	9 in

## Conductor Related

Conductor - ACSR Str Size	795 (54/7) Condor
Conductor - ACSR Str Size Range	795 (54/7) Condor
Conductor - AL Str Size	795.5
Conductor - AL Str Size Range	795.5
Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SA..039024-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YDS45R45RS-SPEC-EN | REV 8/2023