



# YDS4RLS20, Aluminum Full Tension Splice

By Burndy  
Catalog # [YDS4RLS20](#)

Al Compression Full Tension Splice, #4 Smooth Body ACSR  
#200 Grade.

### General

Catalog Number	YDS4RLS20
Connector Type	Splice
Die Index	245
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	621945068636

### Dimensions

Dimension - B Length fraction	5-32/33 in
Dimension - B Length inch	5.97 in
Dimension - Inside Diameter inch	0.31 in
Dimension - L Length Overall mm	306 mm
Dimension - Length Overall inch	12.05 in
Dimension - Outside Diameter inch	0.69 in

### Conductor Related

Conductor - ACSR Str Size	4 (6/1) Swan AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG

Conductor - AL Str Size	4 AWG
Conductor - AL Str Size Range	4 AWG
Conductor Type	<ul style="list-style-type: none"><li>ACSR C Str-Size</li><li>AL C Str-Size</li></ul>

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	3360

### Product Assets

- [3D Models - YDS4RLS20\\_MODEL-IGES](#)
- [3D Models - YDS4RLS20\\_MODEL-STEP](#)
- [3D Models - YDS4RLS20\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30021902](#)
- [Specifications - YDS4RLS20](#)