



# YDS6CA, Aluminum Full Tension Splice, Staked Cable Stop

By Burndy  
Catalog # [YDS6CA](#)



Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension), Die Index:161,3 L.

## General

Connector Type	Splice
Die Index	161
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015391

## Dimensions

Dimension - Inside Diameter inch	0.2 in
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.91 in
Dimension - Outside Diameter inch	0.32 in

## Conductor Related

Conductor - ACSR Cmpt Size	6 AWG
Conductor - ACSR Cmpt Size Range	6 AWG
Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	46400

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - SC019521-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YDS6CA-SPEC-EN | REV 8/2023