

YDS6KT, Copper Full Tension Splice

By Burndy
Catalog # [YDS6KT](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 6A COPPERWELD, Die Index: 162 or 203, Made of copper tubing, Installed with standard tools and dies.

Application

For Copperweld-Copper Conductor

General

Catalog Number	YDS6KT
Connector Type	Splice
Die Index	162;203
EU RoHS Indicator	Yes
Material	Copper
Physical Attribute - Number of Crimps Required	10
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-KT, High Voltage
UPC	781810014578

Dimensions

Dimension - B Length inch	2.83 in
Dimension - L Length Overall mm	154 mm
Dimension - Length Overall inch	6.06 in
Dimension - Pin Diameter inch	0.43 in

Conductor Related

Conductor - CopperWeld Str Size	6 A AWG
---------------------------------	---------

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	11100

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YDS_LineArt](#)
[Sales Drawings - SC24477-01_B](#)
[Specifications - YDS6KT](#)