



YDS6RLS20CG1, Aluminum, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS6RLS20CG1](#)



Single sleeve aluminum UNISPLICE; Full tension aluminum and ACSR applications; prefilled with PENETROX joint compound.

General

| | |
|---------------------------|--------------|
| Catalog Number | YDS6RLS20CG1 |
| Connector Type | Splice |
| Die Index | 165 |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Trade Name | UNISPLICE™ |
| UPC | 621945068759 |

Dimensions

| | |
|-----------------------------------|------------|
| Dimension - B Length fraction | 5-22/25 in |
| Dimension - B Length inch | 5.88 in |
| Dimension - Inside Diameter inch | 0.28 in |
| Dimension - L Length Overall mm | 305 mm |
| Dimension - Length Overall inch | 12 in |
| Dimension - Outside Diameter inch | 0.65 in |

Conductor Related

| | |
|---------------------------------|---|
| Conductor - ACSR Str Size | 6 (6/1) Turkey AWG |
| Conductor - ACSR Str Size Range | 6 (6/1) Turkey AWG |
| Conductor - AL Str Size | 6 AWG |
| Conductor - AL Str Size Range | 6 AWG |
| Conductor Type | <ul style="list-style-type: none">ACSR C Str-SizeAL C Str-Size |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 12 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 2016 |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - sd034930-01](#)
- [Specifications - YDS6RLS20CG1](#)



A Hubbell brand