


YDS75. Copper Full Tension Splice

By Burndy
Catalog # [YDS75](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 1/0 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 165, Made of copper tubing, Installed with standard tools and dies.

Application

For Solid Copper Conductors

General

Catalog Number	YDS75
Connector Type	Splice
Die Index	165;287
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	6
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS
UPC	781810564806

Dimensions

Dimension - B Length inch	2.84 in
Dimension - L Length Overall mm	151 mm
Dimension - Length Overall inch	5.93 in
Dimension - Outside Diameter inch	0.61 in

Conductor Related

Conductor - Copper Solid Size 1/0 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	4900

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YDS_LineArt](#)
[Sales Drawings - SD..015142-02](#)
[Specifications - YDS75](#)