



YDS7K5, Copper Full Tension Splice

By Burndy
Catalog # [YDS7K5](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 9/16 COPPERWELD, Die Index: 344, Made of copper tubing, Installed with standard tools and dies.

General

| | |
|--|--------------|
| Connector Type | Splice |
| Die Index | 344 |
| Material | Copper |
| Physical Attribute - Number of Crimps Required | 5 |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | N |
| Trade Name | HYSPLICE™ |
| UPC | 781810136287 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 4.06 in |
| Dimension - L Length Overall mm | 271 mm |
| Dimension - Length Overall inch | 10.66 in |
| Dimension - Outside Diameter inch | 1.33 in |

Conductor Related

Conductor - CopperWeld Str 4/0 EK AWG
Size

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

Minimum Pack Quantity 1

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SCO21055-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YDS7K5-SPEC-EN | REV 8/2023