

# YDS7M9T, Full Tension Sleeve for Alumoweld

By Burndy  
Catalog # [YDS7M9T](#)



Full Tension Sleeve, 7 #9, 3 #6, 10-3/8 in L, Full-tension splice for Alumoweld transmission lines.

## Features

- Full-Tension splice for Alumoweld transmission lines
- Five connectors accommodate eight conductor sizes
- Sleeve is pre-filled with PENETROX Joint Compound and Capped
- Sleeve is high strength aluminum alloy for optimum corrosion resistance

## Application

For Alumoweld Transmission Lines, Sleeve Is High Strength Aluminum Alloy For Optimum Corrosion Resistance

## General

Catalog Number	YDS7M9T
Connector Type	Splice
Die Index	677
EU RoHS Indicator	Yes
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	FULL TENSION SLEEVE, HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-M-T
UPC	781810015438
UPC 14 Digit GTIN	00781810015438

## Dimensions

Dimension - B Length fraction	5-7/50 in
Dimension - B Length inch	5.14 in
Dimension - L Length Overall mm	264 mm
Dimension - Length Overall inch	10.41 in

Dimension - Outside Diameter 0.8 in  
inch

## Conductor Related

Conductor - AWAC Size	2
Conductor - Alumoweld Size	7#9;3#6
Conductor - Alumoweld Size Range	7#9;3#6

## Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards	RUS
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	No

## Logistics

Carton Quantity	20
Minimum Pack Quantity	1
Pallet Quantity	3360

## Product Assets

[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YDS-M-T\\_LineArt](#)  
[Sales Drawings - SD047272-01](#)  
[Specifications - YDS7M9T](#)