



YDS8KT, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS8KT](#)



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: 8A COPPERWELD, Die Index: 162 or 202, Made of copper tubing, Installed with standard tools and dies.

General

Connector Type	Splice
Die Index	162;202
Material	Copper
Physical Attribute - Number of Crimps Required	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYSPLICE™
UPC	781810820681

Dimensions

Dimension - B Length inch	2.31 in
Dimension - L Length Overall mm	122 mm
Dimension - Length Overall inch	4.80 in
Dimension - Pin Diameter fraction	2/5 in
Dimension - Pin Diameter inch	0.41 in

Conductor Related

Conductor - CopperWeld Str Size	8 A AWG
---------------------------------	---------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	11600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_YDS_LineArt](#)
[Sales Drawings - SC24477-01_B](#)



A proud member of the Hubbell Family.