


## YDS8WG1, Copper, Single Sleeve Full Tension Splice

By Burndy  
Catalog # YDS8WG1



HYSPLICE Single Sleeve Full Tension Splice, Accommodates Wire: #8 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 161, Made of copper tubing, Installed with standard tools and dies.

### Application

For Solid Copper Conductors

### General

Catalog Number	YDS8WG1
Connector Type	Splice
Die Index	161
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of	1
Crimps Required	
Prefilled Oxide Inhibitor	Y
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-W
UPC	781810014615

### Dimensions

Dimension - B Length inch	0.91 in
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.88 in
Dimension - Outside Diameter inch	0.31 in

### Conductor Related

Conductor - Copper Solid Size 8 AWG

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	57600

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_YDS\\_LineArt](#)  
[Sales Drawings - sd015142](#)  
[Specifications - YDS8WG1](#)