



YDSR2RL, Extra Long Replacement Splice

By Burndy
Catalog # [YDSR2RL](#)



Extra long replacement splice designed to facilitate the permanent replacement of an existing line splice. Eliminates need for two splices and extra conductor.

General

Connector Type	Splice
Die Index	BG;687;243
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	781810503188

Dimensions

Dimension - B Length inch	5.04 in
Dimension - L Length Overall mm	711 mm
Dimension - Length Overall inch	28.00 in
Dimension - Outside Diameter inch	.66 in

Conductor Related

Conductor - AAAC 5005 Size	2 AWG
Conductor - AAAC 6201 Size	2 AWG
Conductor - ACSR Str Size	2 AWG
Conductor - AL Str Size	2 AWG
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Size• AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - YDSR2RL_MODEL-STEP](#)
[3D Models - YDSR2RL_MODEL-IGES](#)
[3D Models - YDSR2RL_MODEL-PDF](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 30000688](#)



A proud member of the Hubbell Family.