



# YDSR4RL, Aluminum Extra Long Replacement Splice

By Burndy  
Catalog # [YDSR4RL](#)



Extra long replacement splice designed to facilitate the permanent replacement of an existing line splice. Eliminates need for two splices and extra conductor.

## General

Connector Type	Splice
Die Index	BG;687;243
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	UNISPLICE™
UPC	781810503171

## Dimensions

Dimension - B Length inch	5.47 in
Dimension - L Length Overall mm	626 mm
Dimension - Length Overall inch	24.63 in
Dimension - Outside Diameter inch	.67 in

## Conductor Related

Conductor - AAAC 5005 Size	4 AWG
Conductor - AAAC 6201 Size	4 AWG
Conductor - ACSR Str Size	4 AWG
Conductor - AL Str Size	4 AWG
Conductor Type	<ul style="list-style-type: none"><li>• ACSR C Str-Size</li><li>• AL C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[3D Models - YDSR4RL\\_MODEL-STEP](#)  
[3D Models - YDSR4RL\\_MODEL-PDF](#)  
[3D Models - YDSR4RL\\_MODEL-IGES](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 30000688](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YDSR4RL-SPEC-EN | REV 8/2023