

# Compression Terminal

By Burndy  
Catalog # YE25G49

Terminal plug, 1/0 AWG, 600V-35KV, Tin plated.



## Application

Wire Termination

## General

Connector Type	INLINE PIN
Construction Material - Main	Copper
EU RoHS Indicator	Yes
Feature - Barrel Style	Shrouded
Finish Type	Tin-Plated
Insulation	Y
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	Pin Terminals, HYSEALPLUG
Temperature Rating	194
Trade Name	HYSEALPLUG™
Type	Shrouded Pin Terminals
UPC	781810053409
UPC 12 Digit	7818100534099

## Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.62 in
Dimension - Outside Diameter inch	0.51 in
Dimension - P inch	3.00 in

## Electrical Ratings

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Str Compact Size	1/0 AWG
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Copper Str Size	1/0
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	12000

## Product Assets

[3D Models - YE25G49\\_MODEL-IGES](#)  
[3D Models - YE25G49\\_MODEL-STEP](#)  
[3D Models - YE25G49\\_MODEL-PDF](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 10108813](#)